

# **SPLASH-SHIELD™ SS300**

Protective Clothing Type 4, 5 & 6

## **DESCRIPTION**

The chemical protective clothing is light and has good air permeability. The sewing surface is sealed with adhesive tape help to effectively harmful dry particles and limited liquid spraying & splash.

## **FEATURES**

High permeability, reduce the generation of thermal stress.

Fully elastic cap, ankle, and cuff, maximizes comfort and protection.

Anti-static treatment can help reduce static build-up.

## **APPLICATION**

Biopharmaceutical, agriculture spraying, automotive industry, chemical treatment, pharmaceuticals, handing toxic power, dust-free room, electronic processing, hazardous substances, printing, light industrial clearing & maintenance, food processing, coating.

## **HAZARD TYPE**

Certain limited liquid splash, biological hazards, and solid airborne particle protection (Type 4, 5 & 6), Dust, Light Liquid splash.

# SPLASHSHIELD


# **VERSION**

Three-piece cap, butterfly sleeves, elastic waist, crotch triangle, four-thread sewing.

## **FABRIC**

The outer layer is a high-quality multi-pore membrane, and the inner layer is anti-adhesive polypropylene non-woven cloth, which can provide excellent penetration protection of dust, liquid, blood-borne pathogens

Size - M, L, XL, XXL





J.THADHANI & CO.

New #12/ Old #28, Stringers Street, Chennai - 600001, Tamilnadu, India.



044 - 4262 5223



info@thadhanisafety.com www.thadhanisafety.com













PE 5-B TYPE 6-

EN 1073-2

N 1149-5 EN 1

# **TEST METHOD**

TYPE4 EN14605 provides protection against spraying of chemical liquids.

TYPE5 ENISO13982-1 Provides protection for harmful dry particles.

TYPE6 EN13034 Provides protection against the splashing of light chemical liquids.

EN1073-2 Provides protection for radioactive particles.

EN1149-5 fabric has antistatic property.

EN14126 provides protection against harmful infectious substances.

EN14126 biological hazard and infectious agent test was conducted.

SIZE	Height (A) CM	Chest (B) CM
S	164-170	84-92
М	170-176	92-100
L	176-182	100-108
XL	182-188	108-116
XXL	188-194	116-124
3XL	194-200	124-132







PHYSICAL PERFORMANCE (EN 1073-2)			
Test	Test method	Result	
Abrasion Resistance	EN ISO 12947-2:2016	Class 1	
Puncture Resistance	EN 863:1995	Class 1	
Flex cracking resistance	EN ISO 7854:1997, Method B	Class 6	
Flex cracking resistance at -30° C	EN ISO 7854:1997, Method B	Class 6	
Tensile strength	EN ISO 13934-1:2013	Class 1	
Tear resistance (Trapezoidal)	EN ISO 9073-4:1997	Class 2	
Seam strength	EN ISO 13935-2:2014	Class 3	

Classification of abrasion resistance: Class 1 >10rubs; Class 2 >40rubs; Class 3 >100rubs; Class 4 >400rubs; Class 5 >1000rubs; Class 6 >2000rubs. Hydrostatic head method is used for leak tightness assessment after abrasion.

Classification of puncture resistance: Class 1 >5N; Class 2 >10N; Class 3 >50N; Class 4 >100N; Class 5 >150N; Class 6 >250N.

Classification of leak tightness after compression-folding (Schildknecht) flex cracking resistance: Class 1 >500cycles; Class 2 >1250cycles; Class 3 >3000cycles; Class 4 >8000cycles; Class 5 >20000cycles; Class 6 >50000cycles. Hydrostatic head method is used for leak tightness assessment after compression-folding (Schildknecht) flex cracking.

Classification of leak tightness after compression-folding(Schildknecht) flex cracking resistance at -30° C: Class 1 >100cycles; Class 2 >200cycles; Class 3 >500cycles; Class 4 >1000cycles; Class 5 >2000cycles; Class 6 >4000cycles. Hydrostatic head method is used for leak tightness assessment after compression-folding(Schildknecht) flex cracking resistance at -30° C.

Classification of tensile strength: Class 1 >30N; Class 2 >60N; Class 3 >100N; Class 4 >250N; Class 5 >500N; Class 6 >1000N.

Classification of trapezoidal tear resistance: Class 1 >10N; Class 2 >20N; Class 3 >40N; Class 4 >60N; Class 5 >100N; Class 6 >150N.

Classification of seam strength: Class 1 >30N; Class 2 >50N; Class 3 >75N; Class 4 >125N; Class 5 >300N; Class 6 >500N.

PHYSICAL PERFORMANCE (EN 1073-2)			
Test	Test method	Result	
Abrasion Resistance	EN 530, Method 2	Class 1	
Puncture Resistance	EN 863:1995	No classification	
Resistance to blocking	EN 25978	Class 2	
Tear resistance	EN ISO 9073-4:1997	Class 3	
Seam strength	EN ISO 13935-2:2014	Class 3	

- 1. Classification of abrasion resistance: Class 1 >10rubs; Class 2 >100rubs; Class 3 >500rubs; Class 4 >1000rubs; Class 5 >1500rubs; Class 6 >2000rubs. Visual inspection method is used for leak tightness assessment after abrasion
- 2. Classification of puncture resistance: Class 2 >10N; Class 3 >50N; Class 4 >100N (Remark: Puncture force is 9N).
- 3. Classification of blocking resistance: Class 1 blocking; Class 2 no blocking.
- 4. Classification of tear resistance: Class 1 > 2N; Class 2 > 10N; Class 3 > 20N; Class 4 > 40N; Class 5 > 80N; Class 6 > 150N.
- 5. Classification of seam strength: Class 1 >30N; Class 2 >50N; Class 3 >75N; Class 4 >125N; Class 5 >300N.



REPELLENCY BY CHEMICAL RESULTS (TYPE	PE 6)	
Chemical	Test method	
30% Sulphuric Acid (Fabric) EN ISO 6530:2005		Class 3
10% Sodium Hydroxide	EN ISO 6530:2005	Class 3
O-Xylene	EN ISO 6530:2005	Class 3
Butan-1-ol	EN ISO 6530:2005	Class 3
Classification of repellency to liquids: Class 1 >70	%; Class 2 >80%; Class 3 >90%.	
Classification is according to EN 14325:2018		
RESISTANCE TO PENETRATION OF CHEM	ICAL RESULTS (TYPE 6)	
Chemical	Test method	Result
30% Sulphuric Acid	0% Sulphuric Acid EN ISO 6530:2005	
0% Sodium Hydroxide EN ISO 6530:2005		Class 3
O-Xylene	EN ISO 6530:2005	Class 3
utan-1-ol EN ISO 6530:2005		Class 3
Classification of resistance to penetration by liqui	ds: Class 1 <10%; Class 2 <5%; Class 3<1%	
Classification is according to EN 14325:2018		
PRODUCT WHOLE SUIT TEST PERFORMA	NCE LEVELS	
Standard		Result
Type 5: EN ISO 13982-1:2004/A1:2010		
Protective clothing against solid particulates		Pass
Type 5: Chemical Protective Clothing shall m Whole suit test methods for type 5 Particle inward leakage EN ISO 1398	L s,i	<sub>nn,82/90</sub> ≤30% ≤15%
Type 6: EN 13034:2005+A1:2009		

Type 5: EN 15O 13982-1:2004/A1:2010	Pass	
Protective clothing against solid particulates	F d 3 3	
Type 5: Chemical Protective Clothing shall meet at least the following requirements: L <sub>jmn,82/90</sub> ≤30%		
Whole suit test methods for type 5	≤15%	
Particle inward leakage EN ISO 13982-2:2004		
Type 6: EN 13034:2005+A1:2009	Pass	
Protective clothing against light spray/splash proof	F d 55	
All suits shall pass the test, i.e. the total area on any one undergarment of each suit shall be less than or equal to three times the total calibrated stain area.		
For this suit type, no leakage staining was observed on the dosimeter suit for any of the three suits tested.		
Whole suit test methods for type 6		
Low level spray test ISO 17491-4:2008 method A		
EN 1073-2:2002	Class 1	

Class	Mean value of inward leakage at the three sampling positions inside the suit during exercise of		Nominal protection factor
	One activity (TILE)%	All activity (TIL <sub>A</sub> )%	
3	0.3	0.2	500
2	3	2	50
1	30	20	5

Particle inward leakage EN ISO 13982-2:2004

RESISTANCE TO PENETRATION OF INFECTIVE AGENTS			
Test	Test method	Result	
Resistance to Penetration by Blood-Borne Pathogens - Test method using Phi-X174 Bacteriophage	EN 14126:2003/AC:2004 ISO 16604(2004) procedure D	Class 6	
Resistance to Wet Microbial Penetration	EN 14126:2003/AC:2004 ISO 22610(2006)	Class 6	
Resistance to Liquid Aerosol Penetration	EN 14126:2003/AC:2004 ISO/DIS 22611(2003)	Class 3	
Resistance to Dry Microbial Penetration	EN 14126:2003/AC:2004 ISO 22612(2005)	Class 3	

Classification of Resistance to Penetration by Blood-Borne Pathogens (Hydrostatic pressure at which the material passes the test): Class 1 --- 0kPa; Class 2 --- 1.75kPa; Class 3 --- 3.5kPa; Class 4 --- 7kPa; Class 5 --- 14kPa; Class 6 --- 20kPa.

Classification of Resistance to Wet Microbial Penetration(Breakthrough time, t): Class 1---t≤15min; Class 2--- 15min<t≤30min; Class 3---30min<t≤45min; Class 4--- 45min<t≤60min; Class 5--- 60min <t≤75min; Class 6--- t>75min.

Classification of Resistance to Liquid Aerosol Penetration(Penetration ratio (log)): Class 1--- 1<log≤3; Class 2--- 3<log≤5; Class 3--- log>5.

Classification of Resistance to Dry Microbial Penetration (Penetration (log cfu)): Class 1--- 2<log cfu≤3; Class 2--- 1<log cfu≤2; Class 3---log cfu≤1.

Classification of Resistance to Dry Microbial Penetration (Penetration (log cfu)): Class 1--- 2<log cfu≤3; Class 2--- 1<log cfu≤2; Class 3---log cfu≤1.

Testing & Classification is based on EN 14126: 2003/AC:2004.

The testing has been performed on the garment material. Seams have not been tested.

ELECTROSTATIC PROPERTIES (EN 1149-5: 2018)			
Test	Test method	Result	
Surface resistance	EN 1149-1: 2006	Pass	
EN 1149-5: 2018: Max.2.5×109 $\Omega$ on at least one surface			



# J.THADHANI & CO.

New #12/ Old #28, Stringers Street, Chennai - 600001, Tamilnadu, India.



**044 - 4262 5223** 

