

3M™ Particulate Respirator 9542V, P2/KN95

Technical Data Sheet



ID 1930923
RID 1929944

Description

The 9542V is a disposable specialty respirator with P2 rated filtration that offers protection against certain dusts, mists and fumes. The added carbon layer provides effective relief from nuisance levels* of organic vapours and odours. It is designed to fit a wide range of facial sizes. Its foldable design is portable and easy to carry. Each respirator is individually packaged, protecting it from contamination prior to use.

Features

- Provides protection against mechanically and thermally generated particulates
- 3M™ Cool Flow™ valve: effectively removes heat build-up and provides a cooler and more comfortable wear. The 3M Cool Flow valve also minimises the risk of fogging up eyewear
- Knitted headbands increases wearer comfort
- Disposable and maintenance free
- Lightweight construction promotes greater comfort and increased wear time
- Soft cover web on respirator's inner panel feels comfortable against the wearer's skin
- Added carbon layer provides relief from nuisance levels* of organic vapours and odours
- Adjustable noseclip helps with a custom fit and secure seal
- This product meets the performance requirements of AS/NZS 1716:2012.

Time Use Limitation

- If the respirator becomes damaged, soiled or breathing becomes difficult, leave the contaminated area and then replace and refit the respirator.
- This respirator contains a layer of activated charcoal to remove nuisance levels* of organic vapours and odours. However, if the respirator is worn and fitted correctly and you can smell or detect the contaminant, then replace the respirator as the capacity of the carbon has been exceeded.



Applications

This respirator is suitable for the following suggested applications (but is not limited to):

- Waste disposal and recycling facilities
- Foundry operations
- Printing
- Mining
- Solvent cleaning
- Light welding

Materials

The following materials are used in the production of this product:

Component	Material
Straps	PET, Nylon, Elastane
Staples	Steel
Nose Foam	Polyurethane
Nose Clip	Aluminium
Filter	Polypropylene / Carbon
Valve	Polypropylene and Polyisoprene

This respirator does not contain components made from natural rubber latex or fibreglass.

Weight - 20g per respirator.

Fitting Instructions


Must be followed each time the respirator is worn. Before fitting device, ensure hands are clean.

See Figure 1.

1. Cup respirator in one hand with nosepiece at fingertips, allow headbands to hang freely below hand.
2. Hold respirator under chin, with nosepiece up.
3. Locate the upper strap across the crown of the head and the lower strap below the ears.
4. Straps must not be twisted.
5. Using both hands, mould noseclip to the shape of the nose to ensure a close fit and good seal. Pinching the noseclip using only one hand may result in less effective respirator performance.
6. The seal of the respirator on the face should be fitchecked before entering the workplace. Refer Fit Check section.

Note: Pinching the respirator nosepiece using only one hand may result in less effective respirator fit. Use two hands.

Figure 1



Fit Check

1. Cover the front of the respirator with both hands being careful not to disturb the fit of the respirator.
2. (a) UNVALVED respirator - EXHALE sharply;
(b) VALVED respirator - INHALE sharply.
3. If air leaks around the nose, re-adjust the nose clip to eliminate leakage. Repeat the above fit check.
4. If air leaks at the respirator edges, work the straps back along the sides of the head to eliminate leakage. Repeat the above fit check.

If you **CANNOT** achieve a proper fit **DO NOT** enter the hazardous area. See your supervisor.

It is recommended that wearers be fit tested in accordance with AS/NZS 1715:2009 Standard. For information regarding fit testing procedures, please contact 3M.

Removal Instructions

See Step 3 of Fitting Instructions and place hand over the respirator to maintain position on the face. Pull the bottom strap over the head. Still holding respirator in position, pull the top strap over your head and remove the respirator.

Warnings and Use Limitations

This product meets the performance requirements of AS/NZS 1716:2012.

P2 is the rating given to a respirator that meets AS/NZS1716:2012 for filtering mechanically and thermally generated particles, e.g. those from welding fume.

Respirators with a P2 rating are also recommended for use in certain applications against some pathogenic biological airborne particulates.

1. Failure to follow all instructions and limitations on the use of this respirator and/or failure to wear this respirator during all times of exposure can reduce respirator effectiveness and may result in sickness or death.
2. It is recommended that a face fit test be conducted before assigning a respirator to an individual. If you cannot achieve a proper fit, do not enter contaminated area. See your supervisor.
3. Inspect respirator before each use to ensure it is in good working condition. Examine all the respirator parts for signs of damage including the two straps, noseclip, nose foam and staples. The respirator should be disposed of immediately upon observation of damaged or missing parts.
4. Leave the contaminated area immediately and contact supervisor if dizziness, irritation or other distress occurs.
5. Dispose of used product in accordance with applicable regulations.
6. All respirators should be used in accordance with local regulations.
7. Do not alter, wash, abuse or misuse this respirator.
8. Do not use with beards or other facial hair or other conditions that prevent a good seal between the face and the sealing edge of the respirator.
9. This respirator can help protect the wearer's lungs against certain airborne contaminants; however, it will not prevent entry through other routes such as the skin or eyes, which would require additional personal protective equipment (PPE).
10. This respirator is designed for occupational/professional use by adults who are properly trained in their use and limitations. This respirator is not designed to be used by children.
11. Individuals with a compromised respiratory system, such as asthma or emphysema, should consult a physician and complete a medical evaluation prior to use.
12. Maximum Operating Temperature: + 50 degrees Celsius.
13. The filtration efficiency of this respirator may decrease in the presence of oily mists.
14. This product does not contain components made from natural rubber latex.



THADHANI[®]
The Experts in Safety... Since 1947

Storage Conditions and Shelf Life

Shelf life of unopened product is three (3) years from date of manufacture when stored within temperature range of -20°C to +25°C and at less than 80% relative humidity.

It is recommended that wearers be fit tested in accordance with the AS/NZS 1715:2009 Standard. For information regarding fit testing procedures, contact 3M.

- Activated carbon layer reduces exposure to nuisance levels* of organic vapour and odour, e.g. diesel particulate matter and unburned fuel vapour
- Folded design for easy storage and dispensing in the workplace
- Does not contain components made from natural rubber latex



More comfortable to wear

- The welded knitted headband enhances comfort
- The proprietary 3M Cool Flow Valve is designed for easy exhalation and reduces heat build-up inside the respirator

More comprehensive protection

- Can be used for respiratory protection against solid particles and liquid mists such as those from grinding, sanding, sweeping, sawing, bagging, or processing minerals, coal, iron ore, flour, metal, wood, pollen, and certain other substances
- Applicable to the reduction of odour of dust and organic vapours**
- Applicable to the reduction of dust and non-oil mists generated in industries such as automotive, electrics, chemical, furniture, home appliance, machinery processing and other industries
- Complies with AS/NZS 1716:2012 P2

Ordering Information

SAP ID	Legacy ID	Availability		Model #	Description
		AUS	NZ		
7100224565	XY003892821	•	•	9542V	3M™ Particulate Respirator 9542V, KN95/P2, with Valve and Nuisance Level Organic Vapor Relief, 20 EA/Box, 10 Boxes/Case

Warning

Respirators must not be used until your employer has determined whether usage will be in accordance with manufacturer's instructions. The wearer must be trained in the proper fitting and use of this product. Failure to follow all instructions and warnings on the use of this product and/or failure to wear this respirator during all times of exposure can reduce respirator effectiveness and result in illness or death.

Important Notice

To the extent permitted by law, 3M shall not be liable for any loss or damage including any loss of business, loss of profits, or for any indirect, special, incidental or consequential loss or damage arising from reliance upon any information herein provided by 3M. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence.



THADHANI®
The Experts in Safety... Since 1947

J.THADHANI & CO.

New #12/ Old #28, Stringers Street,
Chennai - 600001, Tamilnadu, India.



044 - 4262 5223



info@thadhanisafety.com



www.thadhanisafety.com